







Low Voltage Insulators ISO-TP and ISO-ADV Metric

Instruction Sheet



INSTRUCTION SHEET



Recommended torques* :

Sizes	M4	M5	M6	M8	M10	M12	M16
Max torques	2 N.m	4 N.m	6 N.m	16 N.m	33 N.m	57 N.m	109 N.m

*Values given for mechanical attachments, using flat washers, tightened with a torque wrench, without lubrication, and with a screw penetration >80% of H length

*Torques given for mechanical uses

WARNING:

1. nVent products shall be installed and used only as indicated in nVent product instruction sheets and training materials. Instruction sheets are available at www.nVent.com and from your nVent customer service representative.
2. nVent products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.
3. All instructions must be completely followed to ensure proper and safe installation and performance.
4. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and/or death, and void your warranty.

SAFETY INSTRUCTIONS: All governing codes and regulations and those required by the job site must be observed. Always use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

RAYCHEM

SCHROFF