

Varistar CP Server Cabinet, RAL 7021, Single, 42 U, 2000H, 600W, 1200D

CATALOG NUMBER

10630-017



Welded steel frame for high static load requirements.
Prepared for 19" integration of IT assets.

FEATURES

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg, dynamic 1000 kg

Ingress protection class IP 20

Installation of different IT equipment possible

Integrated air panels for front to back cooling

Can be easily integrated into aisle containment system

PRODUCT ATTRIBUTES

Rack Height: 42U

Height: 2000mm

Cladding Material: Steel

Width: 600mm

Cladding Color: Black Grey

Depth: 1200mm

Type: Standard

Package Quantity: 1

Dynamic Load: 1000kgf

Cladding Color Code: RAL 7021

Finish: Powder Coated

Frame Material: Steel

Material: Steel

Product Family: Varistar CP

Product Type: Rack

Static Load: 1600kg

Net Weight: 115.02kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE