

EuropacPRO 19" Subrack Kit for Railway, Retrofit Shielding, SNCF

Subrack for Railway applications, conform to SNCF Standard, non-shielded versions.



CERTIFICATIONS





FEATURES

SNCF listed, EuropacPRO-fer, tested to NF F 61-005 and NF F 60-002

The 19" bracket is firmly fixed to the side panel (tox-cold welded) and is especially suited for high mechanical stresses (vibration resistance)

Lateral support bars to NFF standard facilitate insertion of subrack into the (cabinet) frame. The double 19" screwing position adds to additionally safety (NFF standard)

IP 20, in accordance with IEC 60529

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Aluminum construction

Horizontal rail type "Heavy"

SPECIFICATIONS

Static Load: 15kg

Material: Aluminum

Finish: Anodized; Passivated

Complies With: IEC 60297-3-103; SNCF NFF 61005; SNCF NFF 60002

EMC Shielding: No

Product Type: Subrack/Chassis

| Table 1/2 | | | | | | | | | | |
|-------------------|-------------|------------|-------|---------------------|--------------|--------------------|--|--|--|--|
| Catalog Number | Rack Height | Rack Width | Depth | Package Quantity | For Mounting | Board Depth | | | | |
| 21500-070 | 6U | 36HP | 320mm | 1 | Backplane | 220mm | | | | |
| 21500-027 | 6U | 84HP | 320mm | 1 | Backplane | 220mm | | | | |
| 21500-067 | 3U | 36HP | 320mm | 1 | Backplane | 220mm | | | | |
| 21500-029 | 3U | 84HP | 320mm | 1 | Backplane | 220mm | | | | |

| Table 2/2 | | | | | | | | | |
|-------------------|--------------------|-------------------------------------|--------------------|----------|----------------|------------|--|--|--|
| Catalog Number | EMC Gasket Type | Shock and Vibration Tolerance | Handle Included | Mounting | Certifications | Quick Ship | | | |
| 21500-070 | Textile | 5g (force) | Yes | Rack | RoHS | No | | | |
| 21500-027 | Textile | 5g (force) | Yes | Rack | RoHS, SNCF | No | | | |
| 21500-067 | Textile | 5g (force) | Yes | Rack | RoHS | No | | | |
| 21500-029 | Textile | 5g (force) | Yes | Rack | RoHS, SNCF | No | | | |

ADDITIONAL PRODUCT DETAILS

Test reports are available online.

Fer = ferroviaire = French Railways,1 T = 4 HP = 20.32 mmReceptacle/mounting frame for subracks, stainless steel, 9 T or 21 T on request.

Receptacle/mounting frame for subracks, stainless steel, 9 T or 21 T on request.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE