

Plug-In Unit Kit With XL Handle, Shielded, Black, 6 U



The XL handle is used for applications which requires high insertion / extraction forces such as VPX or VXS standards. Suitable for insertion and extractions forces up to 1500N (per pair).

CERTIFICATIONS



FEATURES

For applications which requires high insertion / extraction forces such as VPX or VXS standards

Additional board fixing options available

Handle requires additional die cast fixing block (combination with horizontal rail short / long lip)

U-shaped front panel for textile gasket

Suitable for insertion/extraction forces up to 1500 N (per pair)

IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10

SPECIFICATIONS

Rack Height: 6U

Material: Aluminum

Finish: Anodized; Passivated

Product Type: Front Panel

Type: Front Panel with Handle (PIU)

EMC Shielding: Yes


Table 1/2									
Catalog Number	Rack Width	Package Quantity	Handle Type	Mounting	Gasket Type	Front Finish			
20848-770	8HP	1	XL	Screw-on Front	Textile EMC	Anodized			
20848-771	12HP	1	XL	Screw-on Front	Textile EMC	Anodized			
20848-769	4HP	1	XL	Screw-on Front	Textile EMC	Anodized			

Table 2/2									
Catalog Number	Rear Finish	Treated Edges	Complies With	Height (H)	Width (W)	Quick Ship			
20848-770	Etched	No	IEC 60297-3- 102, IEEE 1101.10, IEEE 1101.1	261.8mm	40.3mm	No			
20848-771	Etched	No	IEC 60297-3- 102, IEEE 1101.10, IEEE 1101.1	261.8mm	60.6mm	No			
20848-769	Etched	No	IEC 60297-3- 102, IEEE 1101.10, IEEE 1101.1	261.8mm	20mm	No			

ADDITIONAL PRODUCT DETAILS

Kit with front panel for micro switch on request.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE