

Plug-In Unit U-Profile Front Panel for IEL, IET, Handle, 3 U



U-Profile front panel can be shielded with a textile gasket. It can be combined with the IEL and IET or the type 2 handle in trapezoid form.

CERTIFICATIONS



FEATURES

For IEL/IET/Trapeziform Type 2 handle

Al extrusion, 2.5 mm, front anodized, rear conductive

U profile, shieldable with textile EMC gasket

Front panel, 3 U, for front mounting

Manufacturing process causes various surface structures to appear between 4 to 12 HP and 14 to 16 HP

Stainless steel alignment pin pressed-in

SPECIFICATIONS

Material: Aluminum

Finish: Anodized; Passivated

Accessory Type: Front panel Product Type: Front Panel

Type: Front Panel for Handle (PIU)

Table 1/3						
Catalog Number	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish	Rear Finish
30848-299	9НР	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized	Conductive
20848-228	11HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized	Conductive
20848-230	14HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized	Conductive
20848-232	16HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized	Conductive

Table 2/3						
Catalog Number	Treated Edges	Complies With	Depth (D)	EMC Shielding	Height (H)	Rack Height
30848-299	No	IEC 60297-3- 102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	2.5mm	No (Retrofittable)	128.4mm	3U
20848-228	No	IEC 60297-3- 102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	2.5mm	No (Retrofittable)	128.4mm	3U
20848-230	No	IEC 60297-3- 102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	2.5mm	No (Retrofittable)	128.4mm	3U
20848-232	No	IEC 60297-3- 102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	2.5mm	No (Retrofittable)	128.4mm	3U

Table 3/3					
Catalog Number	Width (W)	Certifications	Quick Ship		
30848-299	45.38mm		No		
20848-228	55.54mm	RoHS	No		


Catalog Number	Width (W)	Certifications	Quick Ship
20848-230	70.8mm	RoHS	No
20848-232	80.9mm	RoHS	No

ADDITIONAL PRODUCT DETAILS

Please order EMC profile seal separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE