

Drop-In Anchor



CERTIFICATIONS



FEATURES

Internal thread provides easy removal and serviceability

Installs flush or below the base surface

Suitable for redundant non-structural systems on cracked and non-cracked concrete

Fire resistance class R30-R120 for design of anchorages under exposure to fire

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Hole Size (HS)	Length (L)	Drill Bit Diameter
CAM6030	593180	Steel	Electrogalvanized	6 mm	30mm	8mm
CAM8030S6	401154	Stainless Steel 316 (EN 1.4401)		8 mm	30mm	10mm
CAM8030	593190	Steel	Electrogalvanized	8 mm	30mm	10mm

CatalogNumber	Article Number	Material	Finish	Hole Size (HS)	Length (L)	Drill Bit Diameter
CAM10040	593200	Steel	Electrogalvanized	10 mm	40mm	12mm
CAM10040S6	401155	Stainless Steel 316 (EN 1.4401)		10 mm	40mm	12mm
CAM12050	400415	Steel	Electrogalvanized	12 mm	50mm	15mm

Table 2/2

Catalog Number	Article Number	Certifications
CAM6030	593180	CE, 14-0135, CE, 14-0068
CAM8030S6	401154	VdS, CE, 14-0068
CAM8030	593190	CE, 14-0068, VdS, CE, 14-0135
CAM10040	593200	FM Approved, Anchor, CE, 14-0135, CE, 14-0068, VdS
CAM10040S6	401155	CE, 14-0068, VdS
CAM12050	400415	VdS, CE, 14-0135, CE, 14-0068, FM Approved, Anchor


Characteristic Axial Loads from ETA 14-0135

Part Number	Cracked Concrete C20/25	Non-Cracked Concrete C20/25	Standard Embedment Depth
CAM6030	-	2.50 kN	25 mm
CAM8030	-	3.30 kN	30 mm
CAM10040	-	4.40 kN	40 mm
CAM12050	-	6.10 kN	50 mm
CAM8030S6	-	-	-
CAM10040S6	-	-	-

Characteristic Axial Loads from ETA 14-0068 - for redundant non-structural systems

Part Number	Cracked Concrete C20/25	Non-Cracked Concrete C20/25	Standard Embedment Depth
CAM6030	0.80 kN	0.80 kN	25 mm
CAM8030	1.20 kN	1.20 kN	30 mm
CAM10040	1.70 kN	1.70 kN	40 mm
CAM12050	2.60 kN	2.60 kN	50 mm
CAM8030S6	1.20 kN	1.20 kN	25 mm
CAM10040S6	1.70 kN	1.70 kN	40 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

