

EDT2 Enhanced DIN Rail Surge Protection Class II, 3+1 Mode



CERTIFICATIONS



FEATURES

Includes nVent ERICO TD Technology to ensure reliability throughout adverse voltage conditions

Enhanced temporary over voltage (TOV) withstand capability

External back-up fuse is not required up to 315 A (IEC only)

Compact, yet high surge rated pluggable design, using minimum DIN rail width

Retaining clip ensures enhanced vibration and shock resistance performance

Red/Green status indication and change-over contacts standard for remote monitoring


SPECIFICATIONS

Catalog Number	EDT230031R
Nominal System Voltage (Un)	240 V
Max Continuous Operating Voltage (Uc)	300 V L-N 305 V N-PE
Nominal Discharge Current (In), IEC, L-N	20kA 8/20 μ s

Catalog Number	EDT230031R
Nominal Discharge Current (In), IEC, N-PE	40kA 8/20 µs
Max Discharge Current (Imax), IEC, L-N	50kA 8/20 µs
Max Discharge Current (Imax), IEC, N-PE	65kA 8/20 µs
Voltage Protection Level (Up), L-N	1650V
Voltage Protection Level (Up), N-PE	1500V
Back-Up Fuse @ Isccr	250 A @ 50 kA 315 A @ 25 kA
Frequency	50 - 60 Hz
Response Time, L-N	25 ns Max
Response Time, N-PE	100 ns Max
Protection Modes	L-N N-PE
Short Circuit Current Rating (Isccr)	25kA 50kA
Temporary Over Voltage 120 min (Ut/mode), L-N	442 V Withstand
Temporary Over Voltage Withstand 200 ms (Ut), N-PE	1200V
Nominal Discharge Current (In), UL	20kA 8/20 µs
Short Circuit Current Rating (SCCR)	150kA
Voltage Protection Rating (VPR), L-N	1200V
Voltage Protection Rating (VPR), N-PE	1000V
Technology	Thermal Disconnect
Connection, Solid	35 mm² Max
Connection, Stranded	25 mm² Max
Torque (TQ)	4.5 N·m
Humidity	5 - 95
Temperature	-35 to 85 °C
Enclosure Material	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20
Mounting	35 mm top hat DIN rail
Remote Contact Switching Capacity	1 A @ 250 VAC 1 A @ 125 VAC 0.5 A @ 48 VDC 0.5 A @ 24 VDC 0.5 A @ 12 VDC
Remote Contacts	Yes
Status Indication	Mechanical flag

Catalog Number	EDT230031R
Depth (D)	69mm
Height (H)	90 mm
Width (W)	72 mm
Unit Weight	0.37 kg
Certification Details	UL® 1449 Edition 5 Type 1CA
Complies With	EN 61643-11 Type 2 IEC® 61643-11 Class II
Replacement Module	SGT240M EDT2300M

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE