


Labrack C-Rail for 19" Stationary



For assembly to the vertical uprights on the right and left hand side of the 19" plane; especially suited for cable eyes.

CERTIFICATIONS



FEATURES

For assembly to the vertical uprights on the right and left hand side of the 19" plane; especially suited for cable eyes

SPECIFICATIONS

Product Type: C-Rail Material: Steel

Finish: Zinc Plated

Table 1/1				
Catalog Number	Rack Height	Package Quantity	Length	Quick Ship
20118-461	24U	2	1050mm	No
22114-461	39U	2	1650mm	No

ADDITIONAL PRODUCT DETAILS

Please order assembly kit separately. Not suitable on mobile 19" lab racks.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE