

Outdoor Unibody VENT Cabinet



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity.

CERTIFICATIONS



FEATURES

Double-walled, Al

Forced heat dissipation via fan assembled in side panel, max. 35 W/K

IP 55

One-piece inner case with removable outer cladding

SPECIFICATIONS

Material: Aluminum

Table 1/3

Catalog Number	Product Type	Product Family	Rack Height	Height	Width	Depth
11249-007	Outdoor Cabinet	Unibody	16U	930mm	700mm	500mm
11249-012	Outdoor Cabinet	Unibody	25U	1330mm	700mm	500mm

CatalogNumber	Product Type	Product Family	Rack Height	Height	Width	Depth
11249-009	Outdoor Cabinet	Unibody	20U	1100mm	700mm	500mm

Table 2/3

Catalog Number	Wall Type	Door Type	Access	Cooling	EMC Shielding	Complies With
11249-007	Double Walled	Single Door	Front	Fan Ventilation	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
11249-012	Double Walled	Single Door	Front	Fan Ventilation	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
11249-009	Double Walled	Single Door	Front	Fan Ventilation	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

Table 3/3

Catalog Number	Package Quantity	Finish	Quick Ship
11249-007	1	Powder Coated	No
11249-012	1	Powder Coated	No
11249-009	1	Powder Coated	No

ADDITIONAL PRODUCT DETAILS

Please order wall-mounting assembly kit separately.

Further base/plinth heights on request.

Please order panel/slide mounts separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE