


# 3000 Beam Clamp Kit



## FEATURES

Medium duty system

Includes clamp and U channel

## SPECIFICATIONS

**Finish:** Electrogalvanized

**Material:** Steel

Table 1/2

Catalog Number	Article Number	Length (L)	Height (H)	Width (W)	Thickness (T)	Flange Thickness (FT)
3300EG	570410	300mm	15 mm	30 mm	2.5 mm	15 mm Max
3400EG	570420	400mm	15 mm	30 mm	2.5 mm	15 mm Max
3500EG	570430	500mm	15 mm	30 mm	2.5 mm	15 mm Max
3600EG	570440	600mm	15 mm	30 mm	2.5 mm	15 mm Max

Table 2/2

Catalog Number	Article Number	Hole Size (HS)	Static Load 1 (F1)	Static Load 2 (F2)	Static Load 3 (F3)
3300EG	570410	13 mm	3700N	490N	390N

Catalog Number	Article Number	Hole Size (HS)	Static Load 1 (F1)	Static Load 2 (F2)	Static Load 3 (F3)
3400EG	570420	13 mm	3700N	490N	390N
3500EG	570430	13 mm	3700N	490N	390N
3600EG	570440	13 mm	3700N	490N	390N

**Screw Diameter (Sc):** 8

**X:** 10.5 x 25 mm

**D:** 25 mm

**Torque (TQ):** 30 N·m


**E:** 31.5 mm

**A:** 40 mm

**B:** 100 mm

**C:** 150 mm

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

