

Glazed door, 1600x800, Stainless 304, 3mm double bit lock

CATALOG NUMBER

DNGS1608



Electrical components can be viewed while the transparent stainless steel door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

FEATURES

Description: Transparent door fitted with clear safety glass to view the inside of the enclosure. Equipped with double-bit 3 mm lock system and door frame. Allows all options of the locking programme.

Material: Frame: 2 mm AISI 304 stainless steel plate, AISI 316L (on request). Viewing area: 4 mm clear safety glass.

Finish: 400 pre-grained stainless steel.

Protection: IP 55, TYPE 12, 13, IK 07.

Mounting requirements: Use hinge kit DNMKS01 if not for replacement of standard door.

Pack quantity: 1 piece.

PRODUCT ATTRIBUTES

Height: 1600mm

Width: 800mm

Depth: 17mm

Window Size: 1376 x 615mm

Enclosure Material: Mild Steel

Product Family: Free-Standing

Material: Stainless Steel 304

Finish: Brushed

Thickness: 2mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE