

Roof mount Air-to-Water Heat Exchanger, BIT



Industrial roof mount air-to-water heat exchangers remove heat from enclosures by using chilled fluid, which offers a reliable and low maintenance enclosure cooling option.

CERTIFICATIONS



FEATURES

Finish: RAL 7035 for the galvanized steel versions

Internal temperature range: +20 °C to +60 °C

Ambient temperature range: +1 °C to +70 °C

Pack quantity: 1

SPECIFICATIONS

Cable Length: 3m
Protection Rating: IP55

Table 1/1						
Catalog Number	Capacity Watts @ Δt 25°C	Nominal Voltage	Height	Width	Depth	Material
BIT25BX0B	2500W	230V	270mm	400mm	540mm	Galvanized Steel
BIT25BX09	2500W	230V	270mm	400mm	540mm	Stainless Steel
BIT25CX0B	2500W	115V	270mm	400mm	540mm	Galvanized Steel
BIT25CX09	2500W	115V	270mm	400mm	540mm	Stainless Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE