

Thermostat, AAF

Adjustable temperature thermostats and humdistats offer control for installed devices in an enclosure. Devices can turn on or off at the required temperature or humidity level that is set by the user.

SPECIFICATIONS

Table 1/1						
Catalog Number	Height	Width	Depth	Color	Color Code	Finish
C16000385	67mm	50mm	46mm	Light Gray	RAL 7035	Smooth
AAWTS10	64mm	38mm	51mm	Light Gray	RAL 7035	Smooth
AAWTC10	60mm	33mm	35mm	Light Gray	RAL 7035	Smooth
AAWHS10	67mm	50mm	38mm	Light Gray	RAL 7035	Smooth
AAFTO12	60mm	33mm	35mm	Light Gray	RAL 7035	Smooth

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE