

Vertical Mount Slim Series, FLY



This vertical cooling unit,FLY, with a IP55 protection degree, is designed with reduced depth. Available in many different sizes for different cooling requirements. This means that the right cooling solution easily can be chosen.

CERTIFICATIONS



SPECIFICATIONS

Plug Type: 4-pin

Table 1/1

Catalog Number	Height	Width	Depth	Cooling Capacity, L35L35	Cooling Capacity, L35L50	Nominal Voltage
FLY11BT09	1697mm	495mm	195mm	1100W	860W	230V
FLY11BT0B	1697mm	495mm	195mm	1100W	860W	230V
FLY11BTU9	1697mm	495mm	195mm	1100W	860W	230V
FLY11BTUB	1697mm	495mm	195mm	1100W	860W	230V
FLY15BT09	1697mm	495mm	195mm	1500W	1150W	230V
FLY15BT0B	1697mm	495mm	195mm	1500W	1150W	230V
FLY15BTU9	1697mm	495mm	195mm	1500W	1150W	230V
FLY15BTUB	1697mm	495mm	195mm	1500W	1150W	230V
FLY20BT09	1697mm	495mm	195mm	2000W	1550W	230V
FLY20BT0B	1697mm	495mm	195mm	2000W	1550W	230V
FLY20BTU9	1697mm	495mm	195mm	2000W	1550W	230V
FLY20BTUB	1697mm	495mm	195mm	2000W	1550W	230V
FLY25BT09	1697mm	495mm	235mm	2500W	1850W	230V
FLY25BT0B	1697mm	495mm	235mm	2500W	1850W	230V
FLY25BTU9	1697mm	495mm	235mm	2500W	1850W	230V
FLY25BTUB	1697mm	495mm	235mm	2500W	1850W	230V
FLY32BT09	1697mm	495mm	235mm	3200W	2500W	230V

Catalog Number	Height	Width	Depth	Cooling Capacity, L35L35	Cooling Capacity, L35L50	Nominal Voltage
FLY32BT0B	1697mm	495mm	235mm	3200W	2500W	230V
FLY32BTU9	1697mm	495mm	235mm	3200W	2500W	230V
FLY32BTUB	1697mm	495mm	235mm	3200W	2500W	230V
FLY11KT09	1697mm	495mm	195mm	1100W	860W	400V
FLY11KT0B	1697mm	495mm	195mm	1100W	860W	400V
FLY11KTU9	1697mm	495mm	195mm	1100W	860W	400V
FLY11KTUB	1697mm	495mm	195mm	1100W	860W	400V
FLY15KT09	1697mm	495mm	195mm	1500W	1150W	400V
FLY15KT0B	1697mm	495mm	195mm	1500W	1150W	400V
FLY15KTU9	1697mm	495mm	195mm	1500W	1150W	400V
FLY15KTUB	1697mm	495mm	195mm	1500W	1150W	400V
FLY20HT09	1697mm	495mm	195mm	2000W	1550W	400V
FLY20HT0B	1697mm	495mm	195mm	2000W	1550W	400V
FLY20HTU9	1697mm	495mm	195mm	2000W	1550W	400V
FLY20HTUB	1697mm	495mm	195mm	2000W	1550W	400V
FLY25HT09	1697mm	495mm	235mm	2500W	1850W	400V
FLY25HT0B	1697mm	495mm	235mm	2500W	1850W	400V
FLY25HTU9	1697mm	495mm	235mm	2500W	1850W	400V
FLY25HTUB	1697mm	495mm	235mm	2500W	1850W	400V
FLY32HT09	1697mm	495mm	235mm	3200W	2500W	400V

Catalog Number	Height	Width	Depth	Cooling Capacity, L35L35	Cooling Capacity, L35L50	Nominal Voltage
FLY32HT0B	1697mm	495mm	235mm	3200W	2500W	400V
FLY32HTU9	1697mm	495mm	235mm	3200W	2500W	400V
FLY32HTUB	1697mm	495mm	235mm	3200W	2500W	400V

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE