

# nVent CADDY Speed Link SLK with Threaded Stud End



## CERTIFICATIONS



## FEATURES

Complete system includes wire, locking device and pre-assembled threaded stud end fitting

Attaches to structures with threaded anchors or devices with threaded hole

Connects directly to threaded devices in trapeze assemblies, light fixtures, HVAC assemblies or signage

## SPECIFICATIONS

<b>Static Load Safety Factor:</b>	5:1
<b>Finish:</b>	Electrogalvanized
<b>Material:</b>	Steel;Polypropylene;Zinc Alloy
<b>Complies With:</b>	SMACNA HVAC-DCS


Table 1/2

Catalog Number	Wire Rope Diameter	Wire Rope Length	Rod Size (RS)	Screw Length (L)	Height (H)	Width (W)
SLK15L2SE250	1.5 mm	2m	0.25	25mm	55 mm	19 mm

CatalogNumber	Wire Rope Diameter	Wire Rope Length	Rod Size (RS)	Screw Length (L)	Height (H)	Width (W)
SLK15L3SE250	1.5 mm	3m	0.25	25mm	55 mm	19 mm
SLK15L5SE250	1.5 mm	5m	0.25	25mm	55 mm	19 mm
SLK2L2SE250	2 mm	2m	0.25	25mm	55 mm	19 mm
SLK2L5SE250	2 mm	5m	0.25	25mm	55 mm	19 mm
SLK3L1SE375	3 mm	1m	0.375	45mm	62 mm	24 mm
SLK3L2SE375	3 mm	2m	0.375	45mm	62 mm	24 mm
SLK3L3SE375	3 mm	3m	0.375	45mm	62 mm	24 mm
SLK3L7SE375	3 mm	7m	0.375	45mm	62 mm	24 mm

Table 2/2				
Catalog Number	Thickness (T)	Angle (a)	Static Load	Certifications
SLK15L2SE250	12.5 mm	90 ° Max	195N	UL, cUL
SLK15L3SE250	12.5 mm	90 ° Max	195N	UL, cUL
SLK15L5SE250	12.5 mm	90 ° Max	195N	UL, cUL
SLK2L2SE250	12.5 mm	90 ° Max	440N	UL, cUL
SLK2L5SE250	12.5 mm	90 ° Max	440N	UL, cUL
SLK3L1SE375	16 mm	90 ° Max	890N	
SLK3L2SE375	16 mm	90 ° Max	890N	
SLK3L3SE375	16 mm	90 ° Max	890N	
SLK3L7SE375	16 mm	90 ° Max	890N	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

