

nVent CADDY Speed Link SLK with Y-Hook



CERTIFICATIONS



FEATURES

Complete system includes wire, locking device and two pre-assembled hook end fittings

Fastens to the building structure and hooks to hanging services and tray

Spring latch helps provide secure connection

Convenient design allows one hook to be temporarily detached for maintenance or to add cables to the tray

Single drop with double hook provides increased stability to the system

Also available in a single-hook end fitting configuration

SPECIFICATIONS

Wire Rope Diameter:	2 mm
Static Load Safety Factor:	5:1
Finish:	Electrogalvanized
Material:	Steel;Zinc Alloy;Polypropylene
Complies With:	SMACNA HVAC-DCS

Table 1/2

Catalog Number	Article Number	Wire Rope Length	Wire Rope "Y" Length (YL)	A	B	C
----------------	----------------	------------------	---------------------------	---	---	---

SLK2YH500L2	196549	2m	0.5m	58.4 mm	22.9 mm	6.4 mm
SLK2YH500L2R 2	196649	2m	0.5m	58.4 mm	22.9 mm	6.4 mm
SLK2YH500L3	196550	3m	0.5m	58.4 mm	22.9 mm	6.4 mm
SLK2YH500L3R 2	196650	3m	0.5m	58.4 mm	22.9 mm	6.4 mm
SLK2YH500L7	196551	7m	0.5m	58.4 mm	22.9 mm	6.4 mm

Table 2/2

Catalog Number	Article Number	Static Load
SLK2YH500L2	196549	440N
SLK2YH500L2R2	196649	440N
SLK2YH500L3	196550	440N
SLK2YH500L3R2	196650	440N
SLK2YH500L7	196551	440N





Thickness (T): 12.5 mm

Width (W): 19 mm

Height (H): 55 mm

Angle (a): 90 ° Max

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

