

# Push-In Metal Deck Conduit Clamp



## FEATURES

Provides spacing between conduit and deck surface

Easily attached with screw gun or power tool

Permits conduit to be laid out and then attached

Eliminates need for offset bending conduit

## SPECIFICATIONS

**Finish:** nVent CADDY Armour;Pregalvanized

**Material:** Spring Steel;Steel

Table 1/1

Catalog Number	Outer Diameter	Hole Size
AOL12P	19.1 mm	6.4 mm
AOL16P	25.4 mm	6.4 mm
AOL8P	12.7 mm	6.4 mm

## ADDITIONAL PRODUCT DETAILS

No load rating, for positioning only.

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**

