

# Telecom Main Grounding Busbar, 305 mm

## Data Solutions

### CATALOG NUMBER

---

**TMGBA12L15P**



### CERTIFICATIONS

---



### FEATURES

---

Meets TIA-607-C and TIA-607-D and conforms to BICSI® recommendations

Complies with NEMA® standards

Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)

Telecom grounding busbar splice kits are available to extend the length of the busbar

### PRODUCT ATTRIBUTES

---

Material: Copper

Tin Plating: No

Width (W): 101.6mm

Thickness (T): 6.35mm

Length 1 (L1): 305mm

Length 2 (L2): 229mm

Hole Size 1 (HS1): 0.3125in

Hole Size 1 Number of Pairs: 15

Hole Size 2 (HS2): 0.4375in

Hole Size 2 Number of Pairs: 3


A: 25.4mm

B: 28.6mm

C: 15.9mm

D: 15.9mm

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**