

# ProLine Mounting Channel

## Data Solutions



Allows rack angles and other accessories to be positioned at any depth within the cabinet. Rails mount front to back in ProLine frame. Includes two rails, mounting hardware and four M6 spring nuts for mounting accessories. Use hardware kit APSM6CN (package of 20 screws, washers and spring nuts) for mounting additional rack angles or other accessories to the mounting channels.

### FEATURES

Allows rack angles and other accessories to be positioned at any depth within the cabinet

Rails mount front to back in ProLine frame. Includes two rails, mounting hardware and four M6 spring nuts for mounting accessories

Use hardware kit APSM6CN (package of 20 screws, washers and spring nuts) for mounting additional rack angles or other accessories to the mounting channels

### SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material   | Finish        | Color     | Color Code | Thickness |
|----------------|----------------|------------|---------------|-----------|------------|-----------|
| APSM6CN        | 11256          | Mild Steel | Plated        |           |            |           |
| PMU12B         | 14402          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 1.9mm     |
| PMU9B          | 50409          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 1.9mm     |
| PMU11B         | 14401          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 1.9mm     |
| PMU8B          | 50399          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 1.9mm     |

| CatalogNumber | Article Number | Material   | Finish        | Color     | Color Code | Thickness |
|---------------|----------------|------------|---------------|-----------|------------|-----------|
| PMU10B        | 50419          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 1.9mm     |

Table 2/2

| Catalog Number | Article Number | Fits Frame Depth |
|----------------|----------------|------------------|
| APSM6CN        | 11256          |                  |
| PMU12B         | 14402          | 1200mm           |
| PMU9B          | 50409          | 900mm            |
| PMU11B         | 14401          | 1100mm           |
| PMU8B          | 50399          | 800mm            |
| PMU10B         | 50419          | 1000mm           |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**