


TRC Four Pole Distribution Block, 630 A

Data Solutions



CERTIFICATIONS



FEATURES

Transparent protection cover

Bolts included for output connections

Easy accessibility for wiring

Ready to use out of the box, saving installation time and labor

RoHS compliant

SPECIFICATIONS


Catalog Number	TRC-630A
Article Number	563190
Material	Copper Glass Fibre Reinforced Polyamide Plexiglass
Max Working Voltage, IEC (Ui)	1000

Catalog Number	TRC-630A
Peak Short Circuit Current (I _{pk})	84kA
Short Term Withstand Current (I _{cw}) 1s	52kA
Line Side Number of Connections	1
Load Side Number of Connections	8
Hole Size (HS)	10mm
Thread Size (TS)	M8
Depth (D)	60mm
Height (H)	338 – 390mm
Width (W)	340mm
A	290mm
Unit Weight	4.8kg
Flammability Rating	UL® 94V-0
Complies With	IEC® 60439.1 IEC® 61439.1 IEC® 60695-2-11 (Glow Wire Test 960 °C)

ADDITIONAL PRODUCT DETAILS

Line side and load side number of connections are per pole.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE