

# BJ Round Braid with Crimped Lugs



## CERTIFICATIONS



## FEATURES

Ready to use out of the box, saving installation time and labor

Allows for bending very close to the contact area

RoHS compliant

## SPECIFICATIONS

**Material:** Copper  
**Finish:** Tinned  
**Working Temperature:** 105 °C Max

Table 1/2

Catalog Number	Article Number	Ampacity	Cross Section	Length (L)	Wire Diameter	Hole Size (HS)
BJ10-300S	556920	75A	10mm <sup>2</sup>	300mm	0.15mm	6.5 mm
BJ6-150S	556900	45A	6mm <sup>2</sup>	150mm	0.15mm	6.5 mm

CatalogNumber	Article Number	Ampacity	Cross Section	Length (L)	Wire Diameter	Hole Size (HS)
BJ6-200S	556910	45A	6mm <sup>2</sup>	200mm	0.15mm	6.5 mm

Table 2/2

Catalog Number	Article Number	Unit Weight
BJ10-300S	556920	0.03 kg
BJ6-150S	556900	0.01 kg
BJ6-200S	556910	0.01 kg

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**