

APO DT Transparent Hinged Cover Inspection Window with Blanking Inserts



APO DT Covers are designed for use as inspection windows in highly corrosive environments where easy viewing and access is essential.

INDUSTRY STANDARDS

UL Listed Types 3, 3R, 4, 4X, 13

FEATURES

Available sized from 12" x 7" to 24" x 12" (H x W)

DT Covers are maintenance free and corrosion resistant

Frames are made from hot compression molded halogen free, self extinguishing fiberglass reinforced polyester (FRP) that can withstand continuous temperatures from -58°F to 302°F (-50°C to 150°C)

Inspection windows are made from transparent polycarbonate that can withstand continuous temperatures to 248°F (120°C)

Included thumb screw inserts allow quick window opening for access to interior component

Gaskets are made from continuously poured polyurethane foam

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Finish
A41- DTCOVERKIT	A41- DTCOVERKIT	302mm	302mm	45mm	Fiberglass	Smooth Matte
A61- DTCOVERKIT	A61- DTCOVERKIT	603mm	302mm	45mm	Fiberglass	Smooth Matte
A51- DTCOVERKIT	A51- DTCOVERKIT	488mm	302mm	45mm	Fiberglass	Smooth Matte
A71- DTCOVERKIT	A71- DTCOVERKIT	372mm	302mm	45mm	Fiberglass	Smooth Matte
A31- DTCOVERKIT	A31- DTCOVERKIT	302mm	186mm	45mm	Fiberglass	Smooth Matte

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN TRACHTE ILSCO SCHROFF