

# Cable Entry Gland Plate Round Locking Adapter, CCFRM



## FEATURES

CCFRM Locking Adapter only; CCFRBK Frame and CCFRM Counter Nut sold separately

Halogen and silicone free component

The frames, inlays and grommets can be combined in many ways ensuring you many versatile configuration options

No need to disassemble and reconnect connectors on cables so manufactures warranty is not voided

CCFR cable entry is quick and easy to assemble

It is made of a sturdy, glass-fiber reinforced plastic

CCFG grommets needs to be ordered separately

Operating Temperature: -40 to 120 °C / -40 to 248 °F

## SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Finish
CCFRM20A	59669	38mm	38mm	22mm	Thermoplastic Elastomer	Smooth Matte
CCFRM25A	59673	38mm	38mm	22mm	Thermoplastic Elastomer	Smooth Matte
CCFRM32A	59674	38mm	38mm	22mm	Thermoplastic Elastomer	Smooth Matte
CCFRM40A	59675	70mm	70mm	22mm	Thermoplastic Elastomer	Smooth Matte
CCFRM50A	59676	70mm	70mm	22mm	Thermoplastic Elastomer	Smooth Matte
CCFRM63A	59677	70mm	70mm	22mm	Thermoplastic Elastomer	Smooth Matte

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**