

Elbow 45-Degree Lay-in Galvanized



Lay-in Galvanized 45-Degree Elbows are used for continuous run with 45-degree turns. Any side can be removed, retaining lay-in feature regardless of how the elbow is oriented. Lay-in feature allows wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sides are held together with screws.

FEATURES

Lay-in Galvanized 45-Degree Elbows are used for continuous run with 45-degree turns

Any side can be removed, retaining lay-in feature regardless of how the elbow is oriented

Lay-in feature allows wires and cables can be laid in along wireway run

No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system

Sides are held together with screws

SPECIFICATIONS

Finish: Galvanized
Material: Mild Steel

Table 1/1						
Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
F2245EGV	88020	Elbow	64mm	64mm	1.52mm	No
F8845EGV	88800	Elbow	203mm	203mm	1.9mm	No
F121245EGV	89000	Elbow	305mm	305mm	1.9mm	No
F4445EGV	88290	Elbow	102mm	102mm	1.52mm	No
F6645EGV	88580	Elbow	152mm	152mm	1.52mm	No
F101045EGV	45830	Elbow	254mm	254mm	1.9mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE