

Elbow 90-Degree Inside Opening Lay-in Painted



Lay-in Painted 90-Degree Elbow with Inside Opening are used for continuous run with 90-degree turns. Top and inside covers removable so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system.

FEATURES

Lay-in Painted 90-Degree Elbow with Inside Opening are used for continuous run with 90-degree turns

Top and inside covers removable so wires and cables can be laid in along wireway run

No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system

SPECIFICATIONS

Finish: Galvanized

Material: Mild Steel

Table 1/1

Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
F101090EIN	13141	Elbow	254mm	254mm	1.9mm	No
F121290EIN	13142	Elbow	305mm	305mm	1.9mm	No
F2290EIN	13135	Elbow	64mm	64mm	1.52mm	No
F4490EIN	13136	Elbow	102mm	102mm	1.52mm	No
F6690EIN	13137	Elbow	152mm	152mm	1.52mm	No
F8890EIN	13138	Elbow	203mm	203mm	1.9mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE