

# Mounting profiles, CLPF, 40x1925x25mm, Zinc Plated, Mild Steel

## CATALOG NUMBER

**CLPF2000**



The mounting profiles can be fixed in all directions, providing full flexibility for the mounting of accessories, components, and other equipment.

## FEATURES

Description: The CLPF profile system is a 40 mm wide and 25 mm high profile, which can be mounted in all directions on the enclosure's frame. It can also be used in combination with the CLPK and the VB profiles. By turning the profile it can be used as a standard CP20/40 profile in combination with GLM 40/6 sliding nut, to mount installation material which needs adjusting in depth. The profiles, when mounted onto the enclosure's frame are flush with the enclosure's profiles. Two rows of hole patterns for cage nut fixing and self tapping screws are provided. For 90 mm wide profiles two profiles can be mounted next to each other.

Material: Zinc plated steel.

Pack quantity: 4 profiles including snap-line for fixing.

## PRODUCT ATTRIBUTES

Article Number: CLPF2000

Height: 40mm

Width: 1925mm

Depth: 25mm

Compatible Enclosure Height: 2000mm min

Compatible Enclosure Width: 2000mm min

Compatible Enclosure Depth: 2000mm min

Max Load Horizontal C: Only Vertical Loads Allowed

Max Load Horizontal: Only Vertical Loads Allowed

Material: Mild Steel

Finish: Zinc Plated

Thickness: 1.5mm

Package Quantity: 4

Weight: 7.1kg

Enclosure Material: Mild Steel

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE