

ProLine G2 Side Cover



ProLine G2 Solid Sides enclose the open sides of the modular enclosure frame and have innovative design elements incorporated to ensure fast installation and enhanced structural support.

FEATURES

Hinge hanger on top for easy alignment

Formed steel hems on the sides of the covers for enhanced structural support and to protect user from sharp edges

Seamless polyurethane gasket (UL component recognized) provides a water-tight, dust-tight seal against moisture and contaminants

Attach to enclosure frame with low-profile, flat head screws

Door can be reversed without removing the side covers

Used on the sides of the ProLine G2 frame

Not suitable as a barrier between enclosures (instead use the ProLine G2 barrier panel)

Two grounding studs

All mounting hardware included

Side Covers are finished with paint over plated surfaces

SPECIFICATIONS

Color: Light Gray
Color Code: RAL 7035

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Finish
P2CS104	33686	983mm	364mm	20mm	Mild Steel	Powder Coated
P2CS105	31316	983mm	464mm	20mm	Mild Steel	Powder Coated
P2CS106	31317	983mm	564mm	20mm	Mild Steel	Powder Coated
P2CS108	31318	983mm	764mm	20mm	Mild Steel	Powder Coated
P2CS124	33653	1183mm	364mm	20mm	Mild Steel	Powder Coated
P2CS125	31321	1183mm	464mm	20mm	Mild Steel	Powder Coated
P2CS126	31322	1183mm	564mm	20mm	Mild Steel	Powder Coated
P2CS128	31323	1183mm	764mm	20mm	Mild Steel	Powder Coated
P2CS145	31324	1383mm	464mm	20mm	Mild Steel	Powder Coated
P2CS146	33687	1383mm	564mm	20mm	Mild Steel	Powder Coated
P2CS164	31327	1583mm	364mm	20mm	Mild Steel	Powder Coated
P2CS165	31328	1583mm	464mm	20mm	Mild Steel	Powder Coated
P2CS166	31331	1583mm	564mm	20mm	Mild Steel	Powder Coated
P2CS168	31332	1583mm	764mm	20mm	Mild Steel	Powder Coated
P2CS184	31333	1783mm	364mm	20mm	Mild Steel	Powder Coated
P2CS185	31334	1783mm	464mm	20mm	Mild Steel	Powder Coated
P2CS186	31336	1783mm	564mm	20mm	Mild Steel	Powder Coated

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
P2CS2010	31338	1983mm	964mm	20mm	Mild Steel	Powder Coated
P2CS204	31341	1983mm	364mm	20mm	Mild Steel	Powder Coated
P2CS205	31342	1983mm	464mm	20mm	Mild Steel	Powder Coated
P2CS206	31344	1983mm	564mm	20mm	Mild Steel	Powder Coated
P2CS2210	31346	2183mm	964mm	20mm	Mild Steel	Powder Coated
P2CS224	33654	2183mm	364mm	20mm	Mild Steel	Powder Coated
P2CS225	31347	2183mm	464mm	20mm	Mild Steel	Powder Coated
P2CS226	31351	2183mm	564mm	20mm	Mild Steel	Powder Coated
P2CS64	31353	583mm	364mm	20mm	Mild Steel	Powder Coated
P2CS66	31354	583mm	564mm	20mm	Mild Steel	Powder Coated
P2CS68	31355	583mm	764mm	20mm	Mild Steel	Powder Coated
P2CS84	33685	783mm	364mm	20mm	Mild Steel	Powder Coated
P2CS86	31356	783mm	564mm	20mm	Mild Steel	Powder Coated
P2CS88	31357	783mm	764mm	20mm	Mild Steel	Powder Coated
P2CS146HF	31325				Mild Steel	Galvanized, Powder Coated
P2CS148	31326				Mild Steel	Powder Coated
P2CS186HF	31335				Mild Steel	Galvanized, Powder Coated
P2CS188	31337				Mild Steel	Powder Coated
P2CS206HF	31343				Mild Steel	Galvanized, Powder Coated
P2CS208	31345				Mild Steel	Powder Coated

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
P2CS226HF	31348				Mild Steel	Galvanized, Powder Coated
P2CS228	31352				Mild Steel	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE