

Tee Fitting Outside Top Opening Lay-in Hinged Cover



Lay-in Hinged Cover Tee Fitting with Outside Top Opening is used when the covers of two branches are on the same side and the third is on a different side.

INDUSTRY STANDARDS

Certified by Canadian Standards Association.

FEATURES

Lay-in Hinged Cover Tee Fitting with Outside Top Opening is used when the covers of two branches are on the same side and the third is on a different side

SPECIFICATIONS

- Color Code:

ANSI 61
- Finish:

Galvanized; Powder Coated
- Color:

Gray
- Material:

Mild Steel

Table 1/1						
Catalog Number	Article Number	Type	Height	Width	Thickness	Sealing Plate Type
F22LTC	18180	Tee	64mm	64mm	1.9mm	Flat
F44LTC	18410	Tee	102mm	102mm	1.9mm	Flat
F66LTC	18650	Tee	152mm	152mm	1.9mm	Flat
F88LTC	19300	Tee	203mm	203mm	1.9mm	Flat

ADDITIONAL PRODUCT DETAILS

Each sealing plate also includes one gasket and one set of screws to join sections.

Certified by Canadian Standards Association.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDYERICOHOFFMANILSCOSCHROFFTRACHTE