

# Universal Free-Stand Flat End Plate Mild Steel



Flat End plate is used to seal open side(s) of Universal Free-Stand Enclosures. The Flat End Plate provides a low profile cover and is Type 4, 12, 3R, and IP66 rated. Studs welded to the end plate eliminate bolt holes. Gasket and mounting hardware are furnished.

## FEATURES

---

Universal Free-Stand Flat End plate is used to seal open side(s) of nVent HOFFMAN Universal Free-Stand Enclosures.

The Flat End Plate provides a low profile cover and is Type 4, 12, 3R, and IP66 rated

Studs welded to the end plate eliminate bolt holes

Gasket and mounting hardware are furnished

SPECIFICATIONS

**Color Code:** ANSI 61  
**Color:** Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Thickness	Quick Ship
AU9024FEP	60456	2286mm	613mm	7mm	1.98mm	No
AU8424FEP	38974	2137mm	613mm	7mm	1.98mm	No
AU8418FEP	38973	2137mm	460mm	7mm	1.98mm	No
AU9018FEP	60455	2286mm	460mm	7mm	1.98mm	No
AU7218FEP	38972	1832mm	460mm	7mm	1.98mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE