

# Secure Dual W-Lock Power Cord



Secure dual W-Lock power cords provide enhanced cord retention between both the PDU and IT equipment. Both connections require deliberate action in order to release the locking buttons to prevent accidental detachment of power connections. Cords function with any corresponding standard IEC receptacle, but locking feature requires compatible W-lock or V-lock outlets

## FEATURES

Secure dual locking power cords

The IEC C14/C20 plug will lock into any RackPower PDU

The universal locking IEC connector will securely lock into any standard C14/C20 power inlet

Both connections require deliberate action in order to release the locking buttons and disconnect power

## SPECIFICATIONS

Table 1/2

| Catalog Number | Type  | Works With | Length | Color | Height | Input Cable Length |
|----------------|-------|------------|--------|-------|--------|--------------------|
| EP1314024X150  | Cable | RackPower  | 600mm  | Black | 270mm  | 588m               |
| EP1314048X125  | Cable | RackPower  | 1200mm | Black | 270mm  | 1.176m             |
| EP1314072X100  | Cable | RackPower  | 1800mm | Black | 270mm  | 1.764m             |
| EP1314B24X150  | Cable | RackPower  | 600mm  | Blue  | 270mm  | 0.588m             |
| EP1314B48X125  | Cable | RackPower  | 1200mm | Blue  | 270mm  | 1.176m             |

| CatalogNumber | Type  | Works With | Length | Color | Height | Input Cable Length |
|---------------|-------|------------|--------|-------|--------|--------------------|
| EP1314B72X100 | Cable | RackPower  | 1800mm | Blue  | 270mm  | 1.764m             |
| EP1314R24X150 | Cable | RackPower  | 600mm  | Red   | 270mm  | 0.588m             |
| EP1314R48X125 | Cable | RackPower  | 1200mm | Red   | 270mm  | 1.176m             |
| EP1314R72X100 | Cable | RackPower  | 1800mm | Red   | 270mm  | 1.764m             |
| EP1920024X100 | Cable | RackPower  | 600mm  | Black | 270mm  | 0.588m             |
| EP1920048X75  | Cable | RackPower  | 1200mm | Black | 270mm  | 1.176m             |
| EP1920072X50  | Cable | RackPower  | 1800mm | Black | 270mm  | 1.764m             |
| EP1920B24X100 | Cable | RackPower  | 600mm  | Blue  | 270mm  | 0.588m             |
| EP1920B48X75  | Cable | RackPower  | 1200mm | Blue  | 270mm  | 1.176m             |
| EP1920B72X50  | Cable | RackPower  | 1800mm | Blue  | 270mm  | 1.764m             |
| EP1920R24X100 | Cable | RackPower  | 600mm  | Red   | 270mm  | 0.588m             |
| EP1920R48X75  | Cable | RackPower  | 1200mm | Red   | 270mm  | 1.176m             |
| EP1920R72X50  | Cable | RackPower  | 1800mm | Red   | 270mm  | 1.764m             |

Table 2/2

| Catalog Number | Package Quantity | Plug Type | Removable Input Cable | Quick Ship |
|----------------|------------------|-----------|-----------------------|------------|
| EP1314024X150  | 150              | C13/C14   | No                    | No         |

| Catalog Number | Package Quantity | Plug Type | Removable InputCable | Quick Ship |
|----------------|------------------|-----------|----------------------|------------|
| EP1314048X125  | 125              | C13/C14   | No                   | No         |
| EP1314072X100  | 100              | C13/C14   | No                   | No         |
| EP1314B24X150  | 150              | C13/C14   | No                   | No         |
| EP1314B48X125  | 125              | C13/C14   | No                   | No         |
| EP1314B72X100  | 100              | C13/C14   | No                   | No         |
| EP1314R24X150  | 150              | C13/C14   | No                   | No         |
| EP1314R48X125  | 125              | C13/C14   | No                   | No         |
| EP1314R72X100  | 100              | C13/C14   | No                   | No         |
| EP1920024X100  | 100              | C19/C20   | No                   | No         |
| EP1920048X75   | 75               | C19/C20   | No                   | No         |
| EP1920072X50   | 50               | C19/C20   | No                   | No         |
| EP1920B24X100  | 100              | C19/C20   | No                   | No         |
| EP1920B48X75   | 75               | C19/C20   | No                   | No         |
| EP1920B72X50   | 50               | C19/C20   | No                   | No         |
| EP1920R24X100  | 100              | C19/C20   | No                   | No         |
| EP1920R48X75   | 75               | C19/C20   | No                   | No         |
| EP1920R72X50   | 50               | C19/C20   | No                   | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**