

# Varistar CP EMC Shortened Rear Panel with Recessed Mounting Plate



Recessed connection plates are needed for connectors which don't protrude out of the plane of the cabinet

## FEATURES

Intelligent cable management design with recessed connection plates

Connection plate is 400 mm high

For recessed plate: Plate recessed by 40 mm

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Panel

**Protection Rating:** IP55

**Material:** Steel; Stainless Steel

Table 1/1

| Catalog Number | Rack Height | Height | Width | Package Quantity | Finish        | Quick Ship |
|----------------|-------------|--------|-------|------------------|---------------|------------|
| 21630-909      | 38U         | 1800mm | 600mm | 1                | Powder Coated | No         |
| 21630-910      | 38U         | 1800mm | 800mm | 1                | Powder Coated | No         |
| 21630-911      | 42U         | 2000mm | 600mm | 1                | Powder Coated | No         |
| 21630-912      | 42U         | 2000mm | 800mm | 1                | Powder Coated | No         |

| CatalogNumber | Rack Height | Height | Width | Package Quantity | Finish        | Quick Ship |
|---------------|-------------|--------|-------|------------------|---------------|------------|
| 21630-913     | 47U         | 2200mm | 600mm | 1                | Powder Coated | No         |
| 21630-914     | 47U         | 2200mm | 800mm | 1                | Powder Coated | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**