nVent | ERICO

We connect and protect

Conductor Insulation Stripping Tool, 4 x 4

FEATURES

- Provides precision stripping with no conductor damage
- Strips quickly, even in cold climates
- Guarded cutting blades ensure safety
- Bushings change easily with supplied hex wrench

SPECIFICATIONS

Length 1 (L1): 114 mm

Length 2 (L2): 127 mm

Material: Aluminum;Steel

Table 1/1

Catalog Number	Bushing A	Bushing B	Bushing C	Bushing D
SBRT36000906	3/16" Bondstrand, 4/64" Insulation	#6 Sol, 11/64" Insulation	#6 Sol, 12/64" Insulation	#9 Sol, 10/64" Insulation
SBRT360001004	3/16" Bondstrand, 4/64" Insulation	#6 Sol, 11/64" Insulation	#6 Sol, 12/64" Insulation	3/16" Bondstrand, 6/64" Insulation
SBRT360002132	#6 Sol, 6/64" Insulation	#4 Str, 6/64" Insulation	#9 Sol, 5/64" Insulation	3/16" Bondstrand, 6/64" Insulation
SBRT360001010	3/16" Bondstrand, 6/64" Insulation	3/16" Bondstrand, 6/64" Insulation	#6 Sol, 11/64" Insulation	#6 Sol, 12/64" Insulation

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

Our powerful portfolio of brands:
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.