

# EDT2 DIN Rail Surge Protection Replacement Module



## CERTIFICATIONS



## SPECIFICATIONS

| Catalog Number                        | EDT2150M          | EDT2350M          | EDT275M           | EDT2480M          | EDT2300M          |
|---------------------------------------|-------------------|-------------------|-------------------|-------------------|-------------------|
| Nominal System Voltage (Un)           | 120 V             | 277 V             | 60 V              | 400 V             | 240 V             |
| Max Continuous Operating Voltage (Uc) | 150 V             | 350 V             | 75 V              | 480 V             | 300 V             |
| Nominal Discharge Current (In), IEC   | 20kA 8/20 $\mu$ s | 20kA 8/20 $\mu$ s | 20kA 8/20 $\mu$ s | 20kA 8/20 $\mu$ s | 20kA 8/20 $\mu$ s |
| Max Discharge Current (Imax), IEC     | 50kA 8/20 $\mu$ s | 50kA 8/20 $\mu$ s | 50kA 8/20 $\mu$ s | 50kA 8/20 $\mu$ s | 50kA 8/20 $\mu$ s |
| Nominal Discharge Current (In), UL    | 20kA 8/20 $\mu$ s | 20kA 8/20 $\mu$ s | 20kA 8/20 $\mu$ s | 20kA 8/20 $\mu$ s | 20kA 8/20 $\mu$ s |
| Frequency                             | 50 - 60 Hz        | 50 - 60 Hz        | 50 - 60 Hz        | 50 - 60 Hz        | 50 - 60 Hz        |
| Temperature                           | -35 to 85 °C      | -35 to 85 °C      | -35 to 85 °C      | -35 to 85 °C      | -35 to 85 °C      |

| Catalog Number     | EDT2150M                        | EDT2350M                                 | EDT275M                    | EDT2480M                     | EDT2300M                                 |
|--------------------|---------------------------------|------------------------------------------|----------------------------|------------------------------|------------------------------------------|
| Enclosure Material | UL® 94V-0<br>Thermoplastic      | UL® 94V-0<br>Thermoplastic               | UL® 94V-0<br>Thermoplastic | UL® 94V-0<br>Thermoplastic   | UL® 94V-0<br>Thermoplastic               |
| Certifications     | VDE, CE, ERICO<br>EDT2, UR, cUR | VDE, CE, ERICO<br>DT2 Series, UR,<br>cUR | CE, ERICO EDT2,<br>VDE     | VDE, CE, ERICO<br>DT2 Series | CE, ERICO DT2<br>Series, UR, cUR,<br>VDE |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE