

Cable to Web of Rail Mold Only, Power, 85-141 lb T-Rail, 1/0 Concentric, Right Hand

CATALOG NUMBER

PBW2CRH



FEATURES

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

Connections for power or grounding conductor to the neutral axis

PRODUCT ATTRIBUTES

Material: Graphite

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: W

Conductor Size: 1/0 Concentric

Conductor Outer Diameter, Nominal: 9.5mm

Welder Style: T20

Orientation: Right Hand

Mold Only: Yes

Welding Material: PB65 or PB65PLUSF80, Sold Separately

Handle Clamp: C105C, Sold Separately

Conductor Sleeve: S05F, Sold Separately

Hammer Die: WD80, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE