

# Cable to Web of Rail Mold Only, Power, 85-141 lb T-Rail, 4/0 Ropelay, Right Hand

## CATALOG NUMBER

**PBW2SRH**



## FEATURES

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

Connections for power or grounding conductor to the neutral axis

## PRODUCT ATTRIBUTES

Material: Graphite

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: W

Conductor Size: 4/0 Ropelay

Conductor Outer Diameter, Nominal: 15.49mm

Welder Style: T20

Orientation: Right Hand

Mold Only: Yes

Welding Material: PB90 or PB90PLUSF80, Sold Separately

Handle Clamp: C105C, Sold Separately

Conductor Sleeve: S02F, Sold Separately

Hammer Die: WD83, Sold Separately

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**