

Insulated Conductor for Wind Turbine Blade Protection



FEATURES

Insulation cold bend test per UL® 758

SPECIFICATIONS

- Conductor Type:** Smooth Weave
- Flammability Rating:** UL® 94V-0;UL® 1581 VW-1
- Working Temperature:** -40 to 105 °C

Table 1/2						
Catalog Number	Material	Length (L)	Conductor Size	Cross Section	Diameter (Ø)	Insulation Thickness
LPA103IN	Aluminum, Polyvinylchloride		70 mm² Stranded	70mm²	18.5 mm	2 mm
LPA103IN0100.0	Aluminum, Polyvinylchloride	100m	70 mm² Stranded	70mm²	18.5 mm	2 mm
LPA103IN0500.0	Aluminum, Polyvinylchloride	500m	70 mm² Stranded	70mm²	18.5 mm	2 mm
LPC050IN0044.0	Copper, Polyvinylchloride	44m	50 mm² Stranded	50mm²	17.27 mm	2 mm

CatalogNumber	Material	Length (L)	Conductor Size	Cross Section	Diameter (Ø)	Insulation Thickness
LPC050IN0047.0	Copper, Polyvinylchloride	47m	50 mm ² Stranded	50mm ²	17.27 mm	2 mm
LPC050IN0100.0	Copper, Polyvinylchloride	100m	50 mm ² Stranded	50mm ²	17.27 mm	2 mm
LPC103IN	Copper, Polyvinylchloride		70 mm ² Stranded	70mm ²	18.97 mm	2 mm


Table 2/2

Catalog Number	Dielectric Strength
LPA103IN	20
LPA103IN0100.0	20
LPA103IN0500.0	20
LPC050IN0044.0	20
LPC050IN0047.0	20
LPC050IN0100.0	20
LPC103IN	20

ADDITIONAL PRODUCT DETAILS

LPA103IN, LPC050IN and LPC103IN represent the base part number and are orderable in custom lengths.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

☒ **WARNING:** This product can expose you to chemicals including vinyl chloride, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE