

Plinth Base, MSVS



The plinth allows for cabling without any restrictions. Installing cables is made easy as the plinth creates extra space underneath the enclosure.

FEATURES

Description: Four U-section side pieces fixed by screws to the corner sections. Plinth height 100 mm. Machining is required.

Material: 2 mm AISI 304 / AISI 316L pre-grained stainless steel.

Finish: 400 pre-grained stainless steel.

Pack quantity: 1 plinth with mounting material.

SPECIFICATIONS

Thickness: 2mm

Finish: Brushed

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Material	Enclosure Material
MSVS1124-316	MSVS1124-316	100mm	1200mm	400mm	Stainless Steel 316L	Mild Steel
MSVS1083	MSVS1083	100mm	800mm	300mm	Stainless Steel 304	Mild Steel
MSVS1063-316	MSVS1063-316	100mm	600mm	300mm	Stainless Steel 316L	Mild Steel
MSVS1103-316	MSVS1103-316	100mm	1000mm	300mm	Stainless Steel 316L	Mild Steel
MSVS1083-316	MSVS1083-316	100mm	800mm	300mm	Stainless Steel 316L	Mild Steel
MSVS1063	MSVS1063	100mm	600mm	300mm	Stainless Steel 304	Mild Steel
MSVS1103	MSVS1103	100mm	1000mm	300mm	Stainless Steel 304	Mild Steel
MSVS1084	MSVS1084	100mm	800mm	400mm	Stainless Steel 304	Mild Steel
MSVS1124	MSVS1124	100mm	1200mm	400mm	Stainless Steel 304	Mild Steel
MSVS1123-316	MSVS1123-316	100mm	1200mm	300mm	Stainless Steel 316L	Mild Steel
MSVS1084-316	MSVS1084-316	100mm	800mm	400mm	Stainless Steel 316L	Mild Steel
MSVS1123	MSVS1123	100mm	1200mm	300mm	Stainless Steel 304	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE