

MultipacPRO 19" Chassis, Aluminum, Plain Top and Base



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have plain top and bottom cover.

CERTIFICATIONS



FEATURES

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

SPECIFICATIONS

Material:	Aluminum
Finish:	Anodized; Passivated
Product Family:	MultipacPRO
EMC Shielding:	No (Retrofittable)
Type:	Solid

Product Type: Subrack/Chassis

Table 1/2

Catalog Number	Rack Height	Depth	Usable Width	Mounting	Complies With	Certifications
20860-601	1U	220mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-105	RoHS
20860-602	1U	280mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-105	RoHS
20860-603	1U	340mm	403mm	Rack	IEC 60297-3-100	
20860-604	2U	220mm	403mm	Rack	IEC 60297-3-100	
20860-605	2U	280mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-606	2U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-607	3U	280mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-608	3U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-609	3U	400mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-610	3U	460mm	403mm	Rack	IEC 60297-3-100	
20860-611	4U	280mm	403mm	Rack	IEC 60297-3-100	
20860-612	4U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-613	4U	400mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-614	4U	460mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-615	5U	460mm	403mm	Rack	IEC 60297-3-100	RoHS

Table 2/2

Catalog Number	Quick Ship
----------------	------------

20860-601	No
20860-602	No
20860-603	No
20860-604	No
20860-605	No
20860-606	No
20860-607	No
20860-608	No
20860-609	No
20860-610	No
20860-611	No
20860-612	No
20860-613	No
20860-614	No
20860-615	No

ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE