

Plug-In Units Front Panel for Handle Form 1



Flat front panel. Enables the assembly of form 1 trapezoid form extraction handle. The front panel can be shielded with a textile gasket.

CERTIFICATIONS



FEATURES

Front panel, unshielded

Front panel, Al, 2.5 mm, front anodized, rear conductive

SPECIFICATIONS

Material: Aluminum

Finish: Anodized; Passivated

Accessory Type: Front panel Product Type: Front Panel

Type: Front Panel with Handle (PIU)

Table 1/3						
Catalog Number	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
30847-661	3U	6НР	1	Trapezoid, Type	Screw-on Front	Anodized
30847-659	3U	4HP	1	Trapezoid, Type	Screw-on Front	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
30847-660	3U	5HP	1	Trapezoid, Type	Screw-on Front	Anodized
30847-662	3U	7HP	1	Trapezoid, Type	Screw-on Front	Anodized
30847-663	3U	8HP	1	Trapezoid, Type	Screw-on Front	Anodized
30847-666	6U	4HP	1	Trapezoid, Type	Screw-on Front	Anodized
30847-664	3U	10HP	1	Trapezoid, Type	Screw-on Front	Anodized
30847-667	6U	5HP	1	Trapezoid, Type	Screw-on Front	Anodized
30847-665	3U	12HP	1	Trapezoid, Type	Screw-on Front	Anodized
30847-668	6U	6НР	1	Trapezoid, Type	Screw-on Front	Anodized
30847-669	6U	7HP	1	Trapezoid, Type	Screw-on Front	Anodized
30847-670	6U	8HP	1	Trapezoid, Type	Screw-on Front	Anodized
30847-671	6U	10HP	1	Trapezoid, Type	Screw-on Front	Anodized
30847-672	6U	12HP	1	Trapezoid, Type	Screw-on Front	Anodized

Table 2/3						
Catalog Number	Rear Finish	Treated Edges	Complies With	Depth (D)	EMC Shielding	Height (H)
30847-661	Conductive	No	IEC 60297-3- 101, IEEE 1101.1/11	2.5mm	No	128.4mm
30847-659	Conductive	No	IEC 60297-3- 101, IEEE 1101.1/11	2.5mm	No	128.4mm
30847-660	Conductive	No	IEC 60297-3- 101, IEEE 1101.1/11	2.5mm	No	128.4mm


CatalogNumber	Rear Finish	Treated Edges	Complies With	Depth (D)	EMC Shielding	Height (H)
30847-662	Conductive	No	IEC 60297-3- 101, IEEE 1101.1/11	2.5mm	No	128.4mm
30847-663	Conductive	No	IEC 60297-3- 101, IEEE 1101.1/11	2.5mm	No	128.4mm
30847-666	Conductive	No	IEC 60297-3- 101, IEEE 1101.1/11	2.5mm	No	261.8mm
30847-664	Conductive	No	IEC 60297-3- 101, IEEE 1101.1/11	2.5mm	No	128.4mm
30847-667	Conductive	No	IEC 60297-3- 101, IEEE 1101.1/11	2.5mm	No	261.8mm
30847-665	Conductive	No	IEC 60297-3- 101, IEEE 1101.1/11	2.5mm	No	128.4mm
30847-668	Conductive	No	IEC 60297-3- 101, IEEE 1101.1/11	2.5mm	No	261.8mm
30847-669	Conductive	No	IEC 60297-3- 101, IEEE 1101.1/11	2.5mm	No	261.8mm
30847-670	Conductive	No	IEC 60297-3- 101, IEEE 1101.1/11	2.5mm	No	261.8mm
30847-671	Conductive	No	IEC 60297-3- 101, IEEE 1101.1/11	2.5mm	No	261.8mm
30847-672	Conductive	No	IEC 60297-3- 101, IEEE 1101.1/11	2.5mm	No	261.8mm

Table 3/3					
Catalog Number	Width (W)	Quick Ship			
30847-661	30.1mm	No			
30847-659	20mm	No			
30847-660	25mm	No			

Catalog Number	Width (W)	Quick Ship
30847-662	35.2mm	No
30847-663	40.3mm	No
30847-666	20mm	No
30847-664	50.5mm	No
30847-667	25mm	No
30847-665	60.6mm	No
30847-668	30.1mm	No
30847-669	35.2mm	No
30847-670	40.3mm	No
30847-671	50.5mm	No
30847-672	60.6mm	No

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE