


Static Handle Alu-Profile in Trapezoid Form



The static Alu-profile handle, trapezoid form can be mounted to a front panel for extraction of the PCB.

CERTIFICATIONS



FEATURES

Aluminium profile handle

SPECIFICATIONS


Material:	Aluminum
Finish:	Anodized
Works With:	Front Panels
Product Type:	Handle
Type:	Static

Table 1/1

Catalog Number	Rack Width	Package Quantity	Handle Type	Color	Width (W)	Quick Ship
20809-281	3HP	1	Aluminum Profile	Silver	13.8mm	No
20809-284	6HP	1	Aluminum Profile	Silver	29mm	No
20809-286	8HP	1	Aluminum Profile	Silver	39.2mm	No
20809-289	12HP	1	Aluminum Profile	Silver	59.6mm	No
20809-291	21HP	1	Aluminum Profile	Silver	105.2mm	No
20809-292	28HP	1	Aluminum Profile	Silver	140.8mm	No
20809-293	42HP	1	Aluminum Profile	Silver	212mm	No
30809-428		1	Aluminum Profile	Silver	1000mm	No
20809-282	4HP	1	Aluminum Profile	Silver	18.9mm	No
20809-283	5HP	1	Aluminum Profile	Silver	24mm	No
20809-285	7HP	1	Aluminum Profile	Silver	34.1mm	No
20809-287	9HP	1	Aluminum Profile	Silver	44.3mm	No
20809-288	10HP	1	Aluminum Profile	Silver	49.4mm	No
20809-290	14HP	1	Aluminum Profile	Silver	69.7mm	No

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE