

Hex Nut



FEATURES

Internally threaded with a hex drive for many applications

SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Material	Finish	Rod Size	Thickness	Wire Size
010M6	592040	Steel	Electrogalvanized	M6	5 mm	10 mm
010M8S4	592140	Stainless Steel 304 (EN 1.4301)		M8	6.5 mm	13 mm
010M8	592050	Steel	Electrogalvanized	M8	6.5 mm	13 mm
010M10S4	592150	Stainless Steel 304 (EN 1.4301)		M10	8 mm	17 mm
010M12S4	592160	Stainless Steel 304 (EN 1.4301)		M12	10 mm	19 mm
010M12	592070	Steel	Electrogalvanized	M12	10 mm	19 mm
010M16	400444	Steel	Electrogalvanized	M16	13 mm	24 mm

CatalogNumber	Article Number	Material	Finish	Rod Size	Thickness	Wire Size
010M10	592060	Steel	Electrogalvanized	M10		

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

