

TRS Four Pole Distribution Block, 160 A

Data Solutions



CERTIFICATIONS



FEATURES

- Easily fixes onto asymmetric DIN rail or mounts with screws
- Bolts included for output connections
- Transparent protection cover
- Easy accessibility for wiring
- Ready to use out of the box, saving installation time and labor
- RoHS compliant

SPECIFICATIONS


Catalog Number	TRS-160A
Article Number	563160
Material	Copper Glass Fibre Reinforced Polyamide Plexiglass

Catalog Number	TRS-160A
Max Working Voltage, IEC (Ui)	630
Peak Short Circuit Current (Ipk)	34kA
Short Term Withstand Current (Icw) 1s	13.2kA
Line Side Number of Connections	2
Load Side Number of Connections	4
Hole Size (HS)	8mm
Thread Size (TS)	M6
Depth (D)	68mm
Height (H)	150mm
Width (W)	230mm
Unit Weight	1.15kg
Flammability Rating	UL® 94V-0
Complies With	IEC® 60439.1 IEC® 61439.1 IEC® 60695-2-11 (Glow Wire Test 960 °C)

ADDITIONAL PRODUCT DETAILS

Line side and load side number of connections are per pole.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE