

Varistar CP Server Cabinet With Castors

Data Solutions



Welded steel frame for high dynamic load requirements.
Prepared for 19" integration of IT assets.

FEATURES

Preconfigured, ready to use cabinet

High dynamic load 1000 kg with integrated castors, static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different IT equipment possible

Integrated air panels for front to back cooling

Can be easily integrated into aisle containment system

SPECIFICATIONS

Static Load:	1600kg
Product Type:	Rack
Cladding Color Code:	RAL 7021
Frame Material:	Steel

Table 1/2

Catalog Number	Rack Height	Height	Cladding Material	Width	Cladding Color	Depth
----------------	-------------	--------	-------------------	-------	----------------	-------

10630-021	42U	2000mm	Steel	600mm	Black Grey	1200mm
10630-022	42U	2000mm	Steel	800mm	Black Grey	1200mm

Table 2/2					
Catalog Number	Package Quantity	Dynamic Load	Finish	Material	Type
10630-021	1	1000kgf	Powder Coated	Steel	Mobile
10630-022	1	1000kgf	Powder Coated	Steel	Mobile

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE