


Telephone Line Protector



FEATURES

RJ11 sockets provide simple plug-in connection for 4 or 6 position RJ plugs

Includes patch cord and adhesive mounting strips

Provides both L-L and L-PE protection modes for comprehensive protection


Automatic over-current protection

SPECIFICATIONS

Catalog Number	SLP1RJ11A
Max Continuous Operating Voltage (Uc)	280 V
Max Discharge Current (Imax), Per Mode	20kA 8/20 μ s
Voltage Protection Level (Up), T-R	110V
Voltage Protection Level (Up), T/R-G	500 V @ 125 A
Rated Load Current (IL)	120mA
Connection Type	RJ11
Ground Lead Length	150mm
Lead Size	4 mm
Temperature	-40 to 65 °C
Depth (D)	28mm
Height (H)	38 mm
Width (W)	78 mm

Catalog Number	SLP1RJ11A
Unit Weight	0.05 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE