

# Horizontal Pouring Basin, Top Fill, 90°



90 degree top fill horizontal pouring basins are used when structural interferences are directly above the tap hole in the sleeve.

## FEATURES

Made from heat-resistant graphite

Durable, re-usable and long lasting

Designed for use with T-Series and B-Series horizontal top fill sleeves

## SPECIFICATIONS

**Material:** Graphite

Table 1/1

| Catalog Number | Diameter (Ø) | Length 1 (L1) | Length 2 (L2) | Width (W) | Height 1 (H1) | Height 2 (H2) |
|----------------|--------------|---------------|---------------|-----------|---------------|---------------|
| RB TSA9040X    | 38 mm        | 229 mm        | 76 mm         | 76 mm     | 140mm         | 102mm         |
| RB TSA9735X    | 38 mm        | 248 mm        | 76 mm         | 76 mm     | 140mm         | 89mm          |
| RB TSA6040F    | 64 mm        | 152 mm        | 76 mm         | 76 mm     | 140mm         | 102mm         |
| RB TSA9740A    | 41 mm        | 248 mm        | 76 mm         | 76 mm     | 140mm         | 102mm         |
| RB TSA7040J    | 76 mm        | 179 mm        | 76 mm         | 76 mm     | 140mm         | 102mm         |
| RB TSA9040C    | 48 mm        | 229 mm        | 76 mm         | 76 mm     | 140mm         | 102mm         |

| CatalogNumber | Diameter (Ø) | Length 1 (L1) | Length 2 (L2) | Width (W) | Height 1 (H1) | Height 2 (H2) |
|---------------|--------------|---------------|---------------|-----------|---------------|---------------|
| RB TSA9740C   | 48 mm        | 248 mm        | 76 mm         | 76 mm     | 140mm         | 102mm         |
| RB TSA9040D   | 54 mm        | 229 mm        | 76 mm         | 76 mm     | 140mm         | 102mm         |
| RB TSB15045D  | 54 mm        | 381 mm        | 76 mm         | 76 mm     | 152mm         | 114mm         |
| RB TSB12040E  | 57 mm        | 305 mm        | 76 mm         | 76 mm     | 152mm         | 102mm         |
| RB TSA9040F   | 64 mm        | 229 mm        | 76 mm         | 76 mm     | 140mm         | 102mm         |
| RB TSB12042F  | 64 mm        | 305 mm        | 76 mm         | 76 mm     | 152mm         | 108mm         |
| RB TSA9040J   | 76 mm        | 229 mm        | 76 mm         | 76 mm     | 140mm         | 102mm         |
| RB TSB13545J  | 76 mm        | 342 mm        | 76 mm         | 76 mm     | 152mm         | 114mm         |
| RB TSA9040M   | 95 mm        | 229 mm        | 76 mm         | 76 mm     | 140mm         | 102mm         |
| RB TSB12050M  | 95 mm        | 305 mm        | 76 mm         | 76 mm     | 152mm         | 127mm         |
| RB TSB15045M  | 95 mm        | 381 mm        | 76 mm         | 76 mm     | 152mm         | 114mm         |
| RB TSB18550M  | 95 mm        | 470 mm        | 76 mm         | 76 mm     | 152mm         | 127mm         |
| RB TSC18550M  | 95 mm        | 470 mm        | 76 mm         | 76 mm     | 179mm         | 127mm         |
| RB TSC26050M  | 95 mm        | 660 mm        | 76 mm         | 76 mm     | 179mm         | 127mm         |

## ADDITIONAL PRODUCT DETAILS

RB TSA pouring basins require one RBW341 pouring basin frame. RB TSB and RB TSC pouring basins require one RBW341 pouring basin frame and two RBS5000 bolt retainers (all sold separately).

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System Instruction Manual.

Sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE