

# Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 28 HP

## CATALOG NUMBER

**34566-228**



Combinations of horizontal rails and side panels

|                 |                 | „+“ can be combined |   | „-“ combination not recommended |   |
|-----------------|-----------------|---------------------|---|---------------------------------|---|
| Horizontal rail | Rugged x R      | -                   | + | +                               | + |
|                 | Heavy x R       | +                   | + | +                               | + |
|                 | Light x R       | +                   | + | -                               | - |
|                 | Horizontal rail | +                   | + | -                               | - |
| Side panel      | Light x L       | +                   | + | -                               | - |
|                 | Heavy x L       | +                   | + | -                               | - |
|                 | Rugged x L      | +                   | + | -                               | - |
|                 | Horizontal rail | +                   | + | -                               | - |

Light x L, Heavy x L, Rugged x L

The rugged horizontal rail type can handle shock and vibration up to 25 g.

## CERTIFICATIONS



## FEATURES

Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

## PRODUCT ATTRIBUTES

Rack Width: 28HP

Package Quantity: 1

Finish: Anodized

Length: 147.32mm

Material: Aluminum

Product Family: EuropacPRO

Product Type: Horizontal Rail

## ADDITIONAL PRODUCT DETAILS

Without M4 thread to front, without printing and without notch for 19" bracket.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**