

# PropacPRO Complete Desktop Case, Unshielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" assemblies such as plug-in units and euroboards. The aluminum die cast frames and profile sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

## CERTIFICATIONS



## FEATURES

Desktop case, pre-configured in accordance with IEC 60297-3-101 for 19" components

Unshielded

Ventilation slots in base plate

Rear panel perforated

Conforms with DIN EN 62368-1

## SPECIFICATIONS

|                        |                         |
|------------------------|-------------------------|
| <b>Static Load:</b>    | 25kg                    |
| <b>Product Type:</b>   | Case                    |
| <b>Type:</b>           | Case for 19" Components |
| <b>EMC Shielding:</b>  | No (Retrofittable)      |
| <b>Product Family:</b> | PropacPRO               |

Table 1/3

| Catalog Number | Rack Height | Rack Width | Depth | Package Quantity | Usable Height | Usable Width |
|----------------|-------------|------------|-------|------------------|---------------|--------------|
| 24576-001      | 3U          | 28HP       | 266mm | 1                | 112.3mm       | 148mm        |
| 24576-002      | 3U          | 28HP       | 326mm | 1                | 112.3mm       | 148mm        |
| 24576-003      | 3U          | 42HP       | 266mm | 1                | 112.3mm       | 219mm        |
| 24576-004      | 3U          | 42HP       | 326mm | 1                | 112.3mm       | 219mm        |
| 24576-005      | 3U          | 42HP       | 386mm | 1                | 112.3mm       | 219mm        |
| 24576-006      | 3U          | 63HP       | 266mm | 1                | 112.3mm       | 326mm        |
| 24576-007      | 3U          | 63HP       | 326mm | 1                | 112.3mm       | 326mm        |
| 24576-008      | 3U          | 63HP       | 386mm | 1                | 112.3mm       | 326mm        |
| 24576-009      | 3U          | 84HP       | 266mm | 1                | 112.3mm       | 432mm        |
| 24576-010      | 3U          | 84HP       | 326mm | 1                | 112.3mm       | 432mm        |
| 24576-011      | 3U          | 84HP       | 386mm | 1                | 112.3mm       | 432mm        |
| 24576-012      | 3U          | 84HP       | 446mm | 1                | 112.3mm       | 432mm        |
| 24576-013      | 3U          | 84HP       | 506mm | 1                | 112.3mm       | 432mm        |
| 24576-021      | 6U          | 84HP       | 326mm | 1                | 245.7mm       | 432mm        |
| 24576-022      | 6U          | 84HP       | 446mm | 1                | 245.7mm       | 432mm        |

Table 2/3

| Catalog Number | Front Frame Construction | Cooling Option | Complies With   | Finish                    | Height  | Material |
|----------------|--------------------------|----------------|-----------------|---------------------------|---------|----------|
| 24576-001      | Single Piece             | No             | IEC 60297-3-101 | Passivated, Powder Coated | 155.5mm | Aluminum |

| CatalogNumber | Front Frame Construction | Cooling Option | Complies With   | Finish                    | Height  | Material |
|---------------|--------------------------|----------------|-----------------|---------------------------|---------|----------|
| 24576-002     | Single Piece             | No             | IEC 60297-3-101 | Passivated, Powder Coated | 155.5mm | Aluminum |
| 24576-003     | Single Piece             | No             | IEC 60297-3-101 | Passivated, Powder Coated | 155.5mm | Aluminum |
| 24576-004     | Single Piece             | No             | IEC 60297-3-101 | Passivated, Powder Coated | 155.5mm | Aluminum |
| 24576-005     | Single Piece             | No             | IEC 60297-3-101 | Passivated, Powder Coated | 155.5mm | Aluminum |
| 24576-006     | Single Piece             | No             | IEC 60297-3-101 | Passivated, Powder Coated | 155.5mm | Aluminum |
| 24576-007     | Single Piece             | No             | IEC 60297-3-101 | Passivated, Powder Coated | 155.5mm | Aluminum |
| 24576-008     | Single Piece             | No             | IEC 60297-3-101 | Passivated, Powder Coated | 155.5mm | Aluminum |
| 24576-009     | Single Piece             | No             | IEC 60297-3-101 | Passivated, Powder Coated | 155.5mm | Aluminum |
| 24576-010     | Single Piece             | No             | IEC 60297-3-101 | Passivated, Powder Coated | 155.5mm | Aluminum |
| 24576-011     | Single Piece             | No             | IEC 60297-3-101 | Passivated, Powder Coated | 155.5mm | Aluminum |
| 24576-012     | Single Piece             | No             | IEC 60297-3-101 | Passivated, Powder Coated | 155.5mm | Aluminum |
| 24576-013     | Single Piece             | No             | IEC 60297-3-101 | Passivated, Powder Coated | 155.5mm | Aluminum |
| 24576-021     | Single Piece             | No             | IEC 60297-3-101 | Passivated, Powder Coated | 289mm   | Aluminum |
| 24576-022     | Single Piece             | No             | IEC 60297-3-101 | Passivated, Powder Coated | 289mm   | Aluminum |

Table 3/3

| Catalog Number | Protection Rating | Width   | Quick Ship |
|----------------|-------------------|---------|------------|
| 24576-001      | IP20              | 185.9mm | No         |
| 24576-002      | IP20              | 185.9mm | No         |
| 24576-003      | IP20              | 257mm   | No         |

| Catalog Number | Protection Rating | Width   | Quick Ship |
|----------------|-------------------|---------|------------|
| 24576-004      | IP20              | 257mm   | No         |
| 24576-005      | IP20              | 257mm   | No         |
| 24576-006      | IP20              | 363.7mm | No         |
| 24576-007      | IP20              | 363.7mm | No         |
| 24576-008      | IP20              | 363.7mm | No         |
| 24576-009      | IP20              | 470.3mm | No         |
| 24576-010      | IP20              | 470.3mm | No         |
| 24576-011      | IP20              | 470.3mm | No         |
| 24576-012      | IP20              | 470.3mm | No         |
| 24576-013      | IP20              | 470.3mm | No         |
| 24576-021      | IP20              | 470.3mm | No         |
| 24576-022      | IP20              | 470.3mm | No         |

## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**