

# Crimping Compression Tool, Hydraulic

## Data Solutions



### FEATURES

Wide cross section range

Ergonomic design

Lightweight and easy to use

Includes easy-to-carry custom case

### SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Applied Force	System	Dies	Crimping Shape	Conductor Size
M2H	716905	60kN	Hand hydraulic	RKM2 series, PKM2 series	Hexagon	#10 Stranded - 600 kcmil Stranded, 6 mm <sup>2</sup> Stranded - 300 mm <sup>2</sup> Stranded

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**