

# LED Lights for Cabinets

## Data Solutions



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

### CERTIFICATIONS



### FEATURES

Lights can be easily mounted vertically or horizontally.

Simple through-wiring based on a plug-and-play system.

### SPECIFICATIONS

**Product Type:** Light

Table 1/3

| Catalog Number | Input Voltage AC | Accessory Type | Input Voltage DC | Length | Package Quantity | Color |
|----------------|------------------|----------------|------------------|--------|------------------|-------|
| 57274          | 250V max         | Lights         |                  |        | 1                | Black |
| 57275          |                  | Lights         |                  |        | 2                | Black |

| CatalogNumber | Input Voltage AC | AccessoryType | Input Voltage DC | Length | Package Quantity | Color |
|---------------|------------------|---------------|------------------|--------|------------------|-------|
| 57265         | 230V max         | Lights        | 24V max          | 396mm  | 1                | Black |
| 57272         | 250V max         | Lights        |                  | 3000mm | 1                | Black |
| 57273         | 250V max         | Lights        |                  | 1000mm | 1                | Black |

Table 2/3

| Catalog Number | Depth | Finish       | Height | Material | Type                          | Width |
|----------------|-------|--------------|--------|----------|-------------------------------|-------|
| 57274          | 14mm  | Smooth Matte | 53mm   | Plastic  | Cabinet Light, Terminal Block | 18mm  |
| 57275          | 4mm   | Smooth Matte | 30mm   |          | Cabinet Light, Magnet         | 12mm  |
| 57265          | 40mm  | Smooth Matte |        | Plastic  | Cabinet Light                 | 33mm  |
| 57272          |       | Smooth Matte |        | Plastic  | Connection Cable              | 0.3mm |
| 57273          |       | Smooth Matte |        | Plastic  | Cabinet Light                 |       |

Table 3/3

| Catalog Number | Color Temperature | Nominal Voltage | Operating Temperature | Weight | Certifications |
|----------------|-------------------|-----------------|-----------------------|--------|----------------|
| 57274          |                   | 250V            | 60°C min              | 0.07kg |                |
| 57275          |                   |                 |                       | 0.08kg |                |
| 57265          | 5800K             | 230V            | -20 to 55°C           | 0.24kg | RoHS, CE       |
| 57272          |                   | 250V            | 60°C min              |        |                |
| 57273          |                   | 250V            | 60°C min              | 0.3kg  |                |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**