


# Cable to Web of Rail TB5 Complete Welder Pair, Signal



## FEATURES

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis of 85 to 140 lb. rail

## SPECIFICATIONS

Table 1/1

| Catalog Number | Material                       | Rail Type                       | Bond Terminal Style | Conductor Size   | Conductor Outer Diameter, Nominal | Welder Style |
|----------------|--------------------------------|---------------------------------|---------------------|------------------|-----------------------------------|--------------|
| SBTBTB5B       | Steel, Graphite, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 3/4" Tab            | 3/16" Bondstrand | 4.76mm                            | TB5          |
| SBTBTB5C       | Steel, Graphite, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 1" Tab              | 3/16" Bondstrand | 4.76mm                            | TB5          |
| SBTBTB5C12AS   | Steel, Graphite, Thermoplastic | 12 lb ASCE                      | 1" Tab              | 3/16" Bondstrand | 4.76mm                            | TB5          |
| SBTBTB5D       | Steel, Graphite, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 1 1/2" Tab          | 3/16" Bondstrand | 4.76mm                            | TB5          |
| SBTBTB5U       | Steel, Graphite, Thermoplastic | RI60 Girder Rail                | 1" Tab              | 3/16" Bondstrand | 4.76mm                            | TB5          |
| SBXSTB5A       | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 3/4" XS             | 3/16" Bondstrand | 4.76mm                            | TB5          |

| CatalogNumber | Material                       | Rail Type                       | Bond Terminal Style | Conductor Size   | Conductor OuterDiameter, Nominal | Welder Style |
|---------------|--------------------------------|---------------------------------|---------------------|------------------|----------------------------------|--------------|
| SBTBTB5E      | Steel, Graphite, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 1" Tab              | 5/16" Bondstrand | 7.94mm                           | TB5          |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE